



ATTITUDE Junior



ORDER FORM

Rev:05/2025 Valid:10/2025

Errors and imissions excepted

Billing Ad	dress Or Cus	tomer-l	D		Shipping Addro	ess	Identical	To Billing Address
CID:					CID:			
Name:					Name:			
Street:					Street:			
Town/PC:					Town/PC:			
E-Mail:					E-Mail:			
Phone:					Phone:			
Order Info	rmation				User Weight			
Order	Calculation		Built-4-Me®		Max. user weight	:: 100 kg		
Purchase Order					User Weight:	kg		
Art. No.: 4750	0001		Reiml	bursement Code: xxx	Ras	se Price	£	4.969-
Order Date:	Dav	Month	Y	Year	Dua		U U	TIJUJ

107

ATT010804		Junior b gearing, back-pedal brake and parking stability, 16" front wheel, docking syste			4.96
echnical Da	ta Overvi	ew			
lax. user weig	ht	100 kg	Shifter	Twist grip shifter	
ront frame wid		260 – 460 mm	Gears	8	
leight of the at dapters on the		85 g each	Brake	Coaster brake	
otal weight	wileerchan	from 21,5 kg	Parking brake	Rim brake	
/heel size		16"	Frame colors	22	
Vheelchair I	Vlodel - wh	nich will be used in combination with th	e ATTITUDE Junior		ŧ
unrise Medica	l Pediatric	Wheelchairs	Sunrise Medical Whe	elchairs	
Easy Life T			_ Easy Life		
fixed front fra Easy Life RT	me only		fixed front frame on Easy Life R	У	
fixed front fra	me only		 fixed front frame only 	у	-
Youngster 3 please see ne Youngster	ext page for N	loGos in combination with the	_ Xenon/Xenon ² fixed front frame onl	у	-
0			Argon ²		-
			Helium		-
				es are only suitable up to 5°, Please check dealer/ manufacturer if there are any	352
ther Wheelcha	airs				
Sorg Vector		ilable from June 2017, please note: V-Fi	ramas are only suitable up to 59	5	46
Sorg Jump					46
fixed front fra PRO ACTIV Sp	me only, ava beedy / Buddy	ilable from June 2017, please note: V-Fi v	rames are only suitable up to 5°		
		, only suitable up to 5°, Please check wit	th your authorized dealer/ manu	facturer if there are any further NoGos	465
1	ornt fram	e width - measured from outside fror		ame tube	
260 mm			380 mm		
280 mm			400 mm		
300 mm			420 mm		
320 mm			440 mm		
340 mm			460mm		
360 mm					
itting-kits fo	or Youngst	ter 3 Necessary to convert wheel lock	attachment on the Youngster- s	ee pictures on the next page	
	Retro-fit kit	wheel-lock attachment for Youngster (I	Knee-lever-to Standardbrake) in	cl. Standardbrake left & right	19
ATT060150		. Whole fock attachment for foungator (i		on orandarabrako fore a rigite	

Order proces	s information	€
ATT090213	ATTITUDE only - without a related wheelchair order	-
ATT090214	ATTITUDE with wheelchair order - on a seperate wheelchair order form	-

ATT060152 Retro-fit kit wheel-lock mounting brackets for Youngster with Safaribrake

2

ш

Youngster 3: Wheel-lock conversion

To dock the Attitude junior to a Youngster3, the wheel lock attachment needs to be converted- the upper clamp of the Attitude collides with the standard wheel-lock mounting bracket of the Youngster3. If the Youngster3 is equipped with knee-lever brakes, those need to be swapped for Standard-brakes.







ATT060150	Retro-fit kit wheel-lock attachment for Youngster (Knee-lever-to Standardbrake),incl. Standardbrake left & right (Necessary if your Youngster3 is equipped with knee-lever brakes. This kit includes two Standardbrakes (left & right) and mounting brackets)
ATT060151	Retro-fit kit wheel-lock mounting brackets for Youngster with Standardbrake (Necessary if your Youngster3 is already equipped with Standardbrakes. This kit includes mounting brackets)
ATT060152	Retro-fit kit wheel-lock mounting brackets for Youngster with Safaribrake (Necessary if your Youngster3 is already equipped with Safaribrakes. This kit includes mounting brackets)

Youngster 3: NoGos

Short frame (seat-depth ≤ 300 mm)

		COG Position			Wheel lock	
wheel size	1 (passiv)		2 (active)	knee-lever	Standard	Safari
24″	Х		Х	Х	Х	Х
22″	\checkmark		Х	🗸 (1)	(2)	 (3)
20″	\checkmark		✓	🗸 (1)	(2)	🗸 (3)
Long frame (sea	t-depth > 300 mm)					

Long frame (seat-depth > 300 mm)

2019 1010 (000						
		COG Position			Wheel lock	
wheel size	1 (passiv)	2 (middle)	3 (active)	knee-lever	Standard	Safari
24″	✓	✓	Х	🗸 (1)	(2)	🗸 (3)
22″	✓	✓	✓	🗸 (1)	✓ (2)	🗸 (3)
20″	✓	✓	✓	🗸 (1)	(2)	🗸 (3)

(1) knee-lever brake needs to be converted to Standard-brake with retro-fit kit ATT060150

(2) wheel-lock mounting brackets need to be dismounted and swapped for brackets included in retro-fit kit ATT060151 (3) wheel-lock mounting brackets need to be dismounted and swapped for brackets included in retro-fit kit ATT060152


ATTITUDE JUNIOR fork: Angle and depth-adjustability

Angle adjustment:

from 0° (parallel to the ground) to 28° continuosly adjustable

Depth adjustability:

100mm (+/- 50mm compared to standard fork) continuosly adjustable



ork 🔘		
ATT080036	Fork for Attitude Junior, angle and depth-adjustability of crank-position	
res 🕥		
ATT070110	Tyre, pneumatic, tread, Mountainbike	
ATT070111	Tyre, pneumatic, tread, Big Apple	
ear and shi	fters	
ATT070043	Gear hub, 8 speed, coaster brake with grip-shift	
ank and ha	andle - special length, widths and shapes via B4Me 🔘	
ATT080037	Junior crank: length adjustable (2 positions), short: length 110/130mm	
ATT080038	Junior crank: length adjustable (2 positions), long: length 130/150mm	
ATT080039	Junior Handle, horizontal, round, diameter 22mm Grip-shift mounted to the frame	
ATT080023	Handle, vertical, 10° angle, round, diameter 30 mm Grip-shift mounted to the right handle	
	ATT080028 Quad, hand support	2
	ATT080027 Quad, arm support	1
ATT080025	Handle, vertical, 25° angle, oval, diameter 37 x 21 mm Grip-shift mounted to the right handle	
rake		
	Brake, backpedal actuation	
	Additional parking brake with lever mounted to the frame	
ccessories		
ATT090074	Front- & rear lamp	
ATT090080	Speedometer	
ATT090095	Mudguard	
ATT090067	Rear view mirror	
ATT090081	Bottle holder	
ATT090024	High pressure pump 0 - 11 bar	
ATT090085	Bell	
ATT090041	Multitool	
ATT090096	Protection foil	



// Fork for Attitude Junior, angle and depth-adjustability of crank-position







// Tyre, pneumatic, tread, Mountain- // Tyre, pneumatic, tread, Big Apple
bike

Crank and handle





// Gear hub, 8 speed, coaster brake
with grip-shift



// Handle, vertical, 10° angle, round, diameter 30 mm



// Junior crank short: length 110/130mm (2 positions) // Junior Handle, horizontal, round, diameter 22mm

// Quad, hand support



// Quad, arm support



// Handle, vertical, 25° angle, oval, diameter 37 x 21 mm

Accessories





ATT090081



// Bottle holder

// High pressure pump (0 - 11 bar)



ATT090085





// Bell

// Multitool

// Rear view mirror

_

Chain guard Col	ours You can cho	oose separate colo	ours for the frame,	the cranks and the chai	n guard.		
	Frame	Chain guard	Crank		Frame	Chain guard	Crank
01 Matte Black				12 Royal Blue			
02 Gloss Black				13 Brilliant Ocean			
03 Metallic Shadow				14 Scarlet Noir			
04 Starlight White				15 Red Pepper			
05 Silver Ore				16 Cherry Lustre			
06 Storm Gray				17 Turbo Green			
07 Desert Tan				18 Pink Power			
08 Desert Sage				19 Satin Rose			
09 Salute Green				20 Mystic Purple			
10 Velvet Sapphire				21 Solar Orange			
11 Midnight Blue				22 Velocity Yellow			
Sticker colours							

ATT100550 Black

ATT100551 Silver

Comments for special build - please apply for a quote; different lead time and discount structure.

ATTITUDE Manual	€
Base Price	00,000.00
Total Of Additional Equipment	
Packaging And Transport	
Exclusive VAT	
VAT	
Total Price	

Date			Signature	
Day	Month	Year		



Sunrise Medical GmbH

Kahlbachring 2-4 D-69254 Malsch/HD Phone: +49 (0) 72 53 / 9 80-0 Fax: +49 (0) 72 53 / 9 80-222 E-Mail: export@sunrisemedical.de www.SunriseMedical.eu