



"WITHIN 1 HOUR OF DELIVERY I WAS IN THE BUSH AND ON THE BEACH! A DREAM COME TRUE AND PROBABLY ONE OF THE BEST FEELINGS I'VE EVER HAD, ABSOLUTE FREEDOM."

Nick
New South Wales

magic
Mobility™

Extreme X8

**OFF-ROAD
AND OFF
THE MAP**

HIT THE ROAD

Or the sand, or the bush, or the snow.*

*Not to be driven through water

MAKING YOUR CHAIR WORK FOR YOU

Magic Mobility wheelchairs can be found on building sites, farms, stables, national parks - all allowing people to continue to work.



DO YOU KNOW YOUR LIMITS?

The Extreme X8 will help you find them, challenge yourself and embrace your freedom.



V3/AUST/MARCH19

BUILT TO LAST

CUSTOMISED FOR YOUR LIFESTYLE



AUSTRALIAN MADE

Extreme
X8™



MAGIC MOBILITY EXTREME X8

The Magic Mobility Extreme X8 gives you the freedom that you always knew you had. The X8 will be your partner to just about any destination. Sand, snow and every terrain you can throw at it. With unrivaled off-road performance and reliability, the X8 is perfect for outdoor adventurers, explorers and rural workers. If the great outdoors is where you want to be, the Extreme X8 is waiting to take you there.

“WE’VE BEEN
CREATING CUSTOM
MADE VEHICLES
FOR 25 YEARS,
SO THAT YOU CAN
LIVE THE LIFE
YOU CHOOSE”

Ashley Daff
Director



Basic specifications:**

- Length: 1030mm
- Width: 710mm
- Seat to floor height: 470mm (490mm with swing away leg rests)
- Weight limit: 182kg (400lbs), 155kg (340lbs) with lift or tilt
- Top speed: 10kph (6.2mph)
- Motors: 700W Gear in Line
- Wheels: Off-road 14" (145/70-6) black
- Gel Batteries
- Penny and Giles controller with LCD display (R-Net)
- Centre post legrest with one piece footplate
- Sling backrest and rehab seat pan (from 12"-24" wide).

Rehab positioning:

- Power options: 300mm seat lift, tilt (45 degrees), power recline, lay down, power elevating legrests
- Seating and backrests: MPS, rehab backrest, adjustable seat pans and custom seating
- Headrests and mounts: MPS, rehab
- Legrests: centre post, swingaway, power and manual elevating
- Footplates: 1 or 2 piece fixed/flip up/angle adjustable, any custom requirement
- A full range of armpads, straps, pads, harness, restraints, supports are all available from our extensive catalogue.

Options and accessories:

- One-click activator (CJSM 2 or JSM joystick)
- Fold forward back
- Puncture resistant tyre liners
- 24V LED Lighting kit
- USB charger
- Jack
- Luggage rack, bag hooks, bags, pockets, keep safe secret boxes, tables, drinks holder, oxygen and vent carriers
- Special controls: Attendant, head, chin, foot, sip and puff, environmental controls all available
- Crash test compliant tie downs
- RAM mounting system (tablet and swing away tablet holder, mobile phone holder, swing away camera mount, attendant cup holder, action camera holder and cup holder).

Options:



RED - BLACK RIMS



SKY BLUE - BLACK RIMS



TANGERINE - BLACK RIMS

The right wheelchair for:*

- Extreme off-road adventures
- Everyday off-road country living, working and rural productivity
- Active outer urban living.

ATTENTION TO DETAIL

Working together, we can figure out how to make your wheelchair uniquely yours. We know the small touches make a big difference.

BUILT TO LAST

We never compromise on quality. With your wheelchair as your mobility, reliability is paramount. We'd much rather spend time improving our products than repairing them.



ENGINEERED TO THE LAST BOLT

If we think we can make it better, we will. Our in house engineering team are hands on, working side by side with customers and therapists. The entire Magic team work continuously on how we can improve the experience from choosing a Magic Mobility wheelchair to its performance in the places you want to go.



PROUDLY AUSTRALIAN DESIGNED AND MADE

We love that our product is made in Australia. We love meeting our customers, hearing their ever changing needs and taking it back to the drawing board.



Magic Mobility +61 3 8791 5600
sales@magicmobility.com.au

Explore with us magicmobility.com.au



Scan for agent locations

*Please remember that your wheelchair has electric motors and must NEVER be driven through water, into rivers, creeks and the sea
**Specifications subject to change. Check online for current version
**Various model options excluded