# GEMINO – SELECTION GUIDE

## **Choose the Gemino rollator that suits you 100%**

#### GEMINO – SELECTION GUIDE



GEMINO 20

Light-weight design rollator. Great functionality at an attractive price



Indoor and

Everyday use



150-200 cm 135-170 cm (M) 125-165 cm (S) Also suitable for children



Small turning radius for great indoor manoeuvrability













GEMINO 30

Our original 100% rollator. Award-winning design combining high indoor maneuverability with outdoor performance. Lots of colour options and accessories for easy personalization.



Use indoors and out. mainly in the





150-200 cm

135-170 cm (M)

125-165 cm (S)

Also suitable

for children

Small turning





GEMINO30

obstacles with ease.

Designed for comfortable

walking in- and outdoors, also

on uneven terrain. Large, soft

wheels allow negotiating of

150 ka kg 130 kg (M)

Indoor and

outdoor use.

also on uneven

Everday use /

Active use



150-200 cm 135-170 cm (M)

Large, soft



comfort and easy negotiation of obstacles



Extra strong (10 kg load capacity)



version available for easy transportation and lifting Large, soft wheels

GEMINO 30 GEMINO 30

With soft wheels that offer premium

comfort and superior damping to

reduce impact and vibration - even

design, they provide a stylish,

updated look while ensuring a

smoother ride

on uneven grounds. With a modern

Indoor and outdoor

use, also on

uneven terrain

Everday use /

Active use

150 ka

130 kg (M)

150-200 cm

135-170 cm (M)

Small turning

great indoor

manoeuvrability

Super lightweight

5.4 (M)/5.6 kg

radius for





GEMINO 30

For extra secrurity the brakes in the rear wheels will automatically come into action in case of sudden acceleration. Great for gait



Use indoors and out. mainly in the





100 ka



150-200 cm 135-170 cm 125-165 cm (S) Also suitable for children



Small turning radius for great indoor maneuverability In case of





GEMINO30

help with 'freezing'.

Specially designed for people

with Parkinon's. Featuring a

slowdown brake promoting

a steady pace, and a reverse

braking system and laser light to

Use indoors and

Everyday use

130 kg

130 kg (M)

150-200 cm

135-170 cm (M)

Small turning

radius for

great indoor

maneuverability







(P)



Slowdown

break provides





GEMINO 50

Designed for any kind of terrain

and heavy-duty use. Lightweight,

yet rock-solid. All the benefits of

Mostly outdoor

rugged terrain,

occasionally

Active / heavy-

indoors

duty use

150 ka

150 kg (M)

150-200 cm

135-170 cm (M)

use, also on

the award-winning Gemino 30

**GEMINO 60** 

and damping.

The all terrain wheels (ATR) are

ground, making it ideal for winter

conditions and for usage on any

terrain. Enjoy increased comfort

Mostly outdoor

rugged terrain.

Active / heavy-

use, also on

occasionally

indoors

duty use

150 ka

150 kg (M)

150-200 cm

135-170 cm (M)

Extra wide and

long frame for

ultimate stability

Extra-large and

and safety with enhanced grip

designed for use on uneven

GEMINO30

Specially designed for people with Parkinson's, this innovative solution features a slowdown brake that promotes a steady pace, a reverse braking system, and a laser light to combat 'freezing.' It's also designed for comfortable walking on uneven terrain.



outdoor use, also on uneven terrain Everday use /

Indoor and

Active use







Large, soft wheels ensure

and easy

obstacles

Reverse

the rollator

immediately

stops moving

once the brake

braking system

negotiation of

ultimate comfort

135-170 cm (M)



Extra wide and long frame for ultimate stability



soft wheels ensure ultimate comfort and easy negotiation of any obstacle

soft wheels ensure ultimate comfort and easy negotiation of any obstacle



Small turning



GEMINO 50

Optimal support and stability - indoors and out. Combines the comfortable rolling characteristics and stability of the Gemino 60 with the additional support and safety you'd expect from a walker.

Indoor and

terrain

130 ka

outdoor use,

also on uneven

Everyday use /

gait training

130 kg (M)

150-200 cm

adjustable

supports for

extra support

forearm

and stability

135-170 cm (M)



Everyday use /







GEMINO 30

Lightweight walker with

The perfect companion if

gait training

adiustable forearm supports

you need extra support and

stability indoors. Also great for

GEMINO





extra support and stability



Extra wide and long frame for ultimate stability

> and soft wheels ensure ultimate comfort and easy negotiation of

Extra-large




























## **GEMINO RANGE – SPECIFICATIONS**

# GEMINO

### **GEMINO TECHNICAL DATA**



















<b>3 3 6</b>				0	0	9 6	6 6					3	8					9		8			
		GEMINO 20			GEMINO 30 GEMINO 30 Carbon GEMINO 30 Carbon comfort			GEMINO 30 Comfort		GEMINO 50 GEMINO 50ATR			GEMINO 30 Walker		GEMINOSO Walker		<b>GEMINO</b> 30 SpeedControl			<b>GEMINO 3</b> 0 Parkinson		GEMINO 30 comfort parkinson	
		20	20 <b>M</b>	205	30	30 <b>M</b>	30 <b>5</b>	30	30 <b>M</b>	60	60 <b>M</b>	30	30 <b>M</b>	60	GOM	30	30 <b>M</b>	305	30	30 <b>M</b>	30	30 <b>M</b>	
DIMENSIONS							not Carbon																
Maximum user weight	kg	150	130	125	150	130	125	150	130	150	150	150	130	130	130	100	100	100	130	130	150	130	
Recommended user height	cm	150-200	135-170	125-165	150-200	135-170	125-165	150-200	135-170	150-200	135-170	150-200	135-170	150-200	135-170	150-200	135-170	125-165	150-200	135-170	150-200	135-170	
Naximum load capacity in basket	kg	5	5	5	5	5	5	10	10	10	10	5	5	10	10	5	5	5	5	5	5	5	
otal length <b>A</b>	cm	65	65	68	65	65	68	68	68	74	74	65	65	74	74	65	65	68	65	65	68	68	
otal width <b>B</b>	cm	60	60	55	60	60	55	62	62	64	64	60	60	64	64	60	60	55	60	60	62	62	
	0111				7.1 (7.4)	7.0 (7.3)		02	02	0.5 (0.0)	0.0 (0.5)	40.0 (40.0)	40.4 (40.7)	44.0 (40.4)	44.0 (44.0)	0.7 (0.0)	0.0 (0.0)	0.0 (0.4)	7.5 (7.0)	7.4/7.7\	0.4 (0.4)	7.0 (0.4)	
otal weight without basket (with basket)	kg	7.1 (7.3)	7.0 (7.2)	6.8 (6.6)	5.6 (5.9) Carbon		6.6 (6.8)	7.7 (8)	7.5 (7.8)	8.5 (8.8)	8.2 (8.5)	10.6 (10.9)	10.4 (10.7)	11.8 (12.1)	11.6 (11.9)	8.7 (8.9)	8.6 (8.8) 47	8.2 (8.4)	7.5 (7.8)	7.4 (7.7)	8.1 (8.4) 47	7.9 (8.1) 47	
Vidth between centre of push handles <b>©</b>	cm	47	47	42	47	47	42	47	47	51 62	51	62	55	45 62	45 53	47 62	55	42	47 62	47 55	64	57	
Seat height <b>D</b>	cm	62	55	48	62	55	48	64	57	02	33	02	33	02	33	02	33	40	02	33	04	3/	
						69 - 88				76-95	73 - 83	98 - 115	84 - 100	98 - 115	89 - 98	78 - 100	69 - 88	65 - 77	78 - 100	69 - 88	80 - 102	71 - 90	
otal height 😉	cm	78 - 100	69 - 88	65 - 77	78 - 100	73 - 88 Carbon	65 - 77	80 - 102	71 - 90	84	80	97	89	109	101	80	76	69	80	76	82	77	
otal height folded	cm	80	76	69	80	76	69	82	77	74	74	65	65	74	74	65	65	68	65	65	68	68	
otal lenght folded	cm	65	65	68	65	65	68	68	68	23	23	35.5	35.5	35.5	35.5	23	23	23	23	23	23	23	
otal width folded	cm	23	23	23	23	23	23	23	23	28 x 4.2	28 x 4.2	20 x 3.6	20 x 3.6	28 x 4.2	28 x 4.2	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	23 x 4.2	23 x 4.2	
Diameter front wheels 🕞	cm	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	23 x 4.2	23 x 4.2	23 x 4.2	23 x 4.2	20 x 3.6	20 x 3.6	23 x 4.2	23 x 4.2	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	23 x 4.2	23 x 4.2	
Diameter rear wheels <b>G</b>	cm	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	23 x 4.2	23 x 4.2														
PERFORMANCE										95	95	84	84	95	95	84	84	79	84	84	84	84	
urning radius	cm	84	84	79	84	84	79	88	88														
COLOUR OPTIONS																							
Black					√	√ for Carbon M only	,			√	√	√	√	√	√	$\sqrt{}$	√	√	√	√	$\checkmark$	√	
ilver grey					√ not Carbon	√ not Carbon	√	√	√														
hampagne					√ not Carbon	√ not Carbon												√	$\sqrt{}$				
Sapphire blue					√ not Carbon	√ not Carbon	√	√	$\sqrt{}$									$\sqrt{}$					
ink					√ not Carbon		√																
pple green					√ not Carbon	√ not Carbon																	
carlett red					√ not Carbon			√	$\checkmark$														
ERTIFICATES										$\sqrt{}$	$\sqrt{}$	√	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	√	$\sqrt{}$	√	$\sqrt{}$	√	
E		$\sqrt{}$	√	$\sqrt{}$	$\checkmark$	√	√	√	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	$\checkmark$	√	$\sqrt{}$	√	$\sqrt{}$	$\sqrt{}$	
N 12182		$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	√	$\sqrt{}$	√	√	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$					$\sqrt{}$	$\sqrt{}$	√	$\sqrt{}$	√	$\sqrt{}$	$\sqrt{}$	
SO 11199-2		√	√	√	√	√	√	√	√			√	√		√								

Gemino Walker rollators: EN 12182, ISO 11199-3 - All other Gemino rollators: EN 12182, ISO 11199-2

